

FoodPro Series Temperature measurement instruments





NSF

Scan Quickly scan temperatures without risk of cross-contamination

Probe Verify internal temperatures with flip down probe thermometer (FoodPro Plus unit only)


Timer Set adjustable alarms for line check reminders (FoodPro Plus unit only)

HACCP Check Indication lights instantly warn of potentially unsafe temperatures

Hand Washable Sealed to IP54 standards for long life expectancy and accuracy

Spot Illumination Target IR measurements highlighted by LED

Extended Life Two year warranty standard for normal use



The Fluke FoodPro™ thermometer series provides advanced temperature measurement solutions for the foodservice industry.

Foodservice professionals understand the need for complete, accurate and fast temperature monitoring from point of receiving through holding and serving. Monitoring temperature is essential to keeping food safe, and is required by the Food and Drug Administration (FDA). Regular monitoring of temperatures and adherence to food safety guidelines makes for better business—increasing food safety and reducing liability and food waste. The combination of both FoodPro thermometers provides a complete temperature measurement and monitoring solution for foodservice professionals

FoodPro Thermometer

The first line of defense

The FoodPro non-contact thermometer is the first line of defense in the battle against improper receiving, storage and holding temperatures. Using infrared, the highly accurate FoodPro quickly reads surface temperatures, allowing workers to make rapid and frequent temperature measurements faster than contact units and without fear of cross contamination. The easy-to-see illumination light shows the temperature measurement spot and removes the targeting guesswork.







FoodPro Plus Thermometer

The total temperature solution








The Fluke FoodPro Plus is a combination infrared surface temperature scanner and probe thermometer with an integrated count-down timer to monitor line checks and cooking and cooling intervals. Infrared readings feature a target illumination light to quickly locate and highlight the measurement spot; the dual-reading display shows the highest scanned temperature alongside the current reading. The quick response, field replaceable RTD (Resistant Thermal Device) platinum tipped probe does not need recalibration. The FoodPro Plus is a rugged, long term and indispensable tool for every type of foodservice establishment.

A multitude of uses in every kitchen and facility





Deep fryers



Probe meat and poultry



Cold storage



Preparing foods



Steam tables and salad bars



IP54 sealed for easy cleanup

Non-contact line checks

Industry standards require internal temperature measurements for line checks to be taken with a probe 1 in. (25 mm) below the surface (2001 NSF/ANSI 7 standard, section 6.3.2). To apply a similar method with the Fluke FoodPro, push back food 1 in. (25 mm) deep and take the temperature with an infrared scan. Line checks can be accomplished 10-20 times faster when using a fast response infrared thermometer compared to a contact unit, and at the same time eliminate cross contamination risk.

HACCP check

Spotting critical temperatures has never been easier or faster. The HACCP Check "Go/No-Go" lights on all FoodPro models show immediately if temperatures are within HACCP guidelines for safe hot or cold food holding. A green light indicates safe hot and cold holding temperatures, while potentially dangerous food temperatures trigger a red light.

The FDA has recommended HACCP (Hazard Analysis Critical Control Points) temperature thresholds where time and temperature rules apply. These guidelines are recommended to food service professionals and institutions for controlling the temperatures that product should be stored, cooked, or cooled to, as well as the length of time food products can safely remain at specific temperatures.¹

For more information on HACCP and Fluke instruments, visit www.fluke.com/foodservice

| | Safer | Risk Zone | Safer | | |
|--------------------------------|-------------------------|---|---|--|--|
| | Chilled and zen Storage | Ripening Fermenting Warming-Cooling | Pasteurization Sterilization Conservation Warm Holding | | |
| Microorganism growth inhibited | | Heavy growth of microorganisms | Microorganism growth inhibited or destroyed | | |
| | 4 °C | 4 °C to 60 °C | 60 °C | | |
| | 40 °F | 40 °F to 140 °F | 140 °F | | |
| | | | | | |
| | | | | | |
| | | ⊕ № Ⅲ | | | |
| HOLD | | | | | |

^{1.} U. S. Department of Health and Human Services, Public Health Service, Food and Drug Administration, 1997 Food Code, Annex





| | | FoodPro | FoodPro Plus |
|---|----------------------------------|--|--|
| Temperat | ture Range | -30 °C to 200 °C (-20 °F to 400 °F) | -35 °C to 275 °C (-30 °F to 525 °F) |
| | | Between 0 °C and 65 °C (32 °F to 150 °F): \pm 1 °C (\pm 2 °F) Below 0 °C (32 °F): \pm 1 °C (\pm 2 °F) \pm 0.1 degree/degree Above 65 °C (150 °F): \pm 1.5 % of reading | Between 0 °C and 65 °C (32 °F to 150 °F): \pm 1 °C (\pm 2 °F) Below 0 °C (32 °F): \pm 1 °C (\pm 2 °F) \pm 0.1 degree/degree Above 65 °C (150 °F): \pm 1.5 % of reading |
| Response | Time | < 500 ms after initial reading | < 500 ms after initial reading |
| Spectral | response | 8-14 microns | 8-14 microns |
| Emissivit | у | Pre-set for food service applications | Pre-set for food service applications |
| | to Spot Size/ esolution (D:S) | 2.5:1 @ 90 % energy, typical | 2.5:1 @ 90 % energy, typical |
| Typical V | Vorking Range umination) | ≈25 mm to 250 mm (≈1 in to 10 in) | ≈25 mm to 250 mm (≈1 in to 10 in) |
| Minimum | 1 Target Size | 12 mm (0.5 in) Ø | 12 mm (0.5 in) Ø |
| Illuminat IR Chann | | 13 mm (0.52 in) | 13 mm (0.52 in) |
| Temperat | ture Range | - | -40 °C to 200 °C (-40 °F to 390 °F) |
| Accuracy (Assumes operating of 23 °C ± | | - | Between -5 °C and 65 °C (23 °F to 150 °F): \pm 0.5 °C (\pm 1 °F) Below -5 °C (23 °F): \pm 1 °C (\pm 2 °F) Above 65 °C (150 °F): \pm 1 % of reading |
| Response | e Time | - | 7-8 seconds (3 time constants) |
| operating of 23 °C ± Response Probe Dir | mensions | - | Diameter: 3.0 mm (0.118 in) Length: 80 mm (3.0 in) |
| Sensor T | уре | - | Thin-film Platinum, Class A, Resistance Thermal Device (RTD) |
| Repeatab | ility | Within the accuracy specifications of the unit | Within the accuracy specifications of the unit |
| Ambient (| Operating Range | 0 °C to 50 °C (32 °F to 122 °F) | 0 °C to 50 °C (32 °F to 122 °F) |
| Relative l | | 90 % (± 5%) RH non-condensing @30 °C (86 °F) | 90 % (± 5 %) RH non-condensing @30 °C (86 °F) |
| | Temperature | -20 °C to 60 °C (-4 °F to 140 °F) | -20 °C to 60 °C (-4 °F to 140 °F) |
| (with Batt | Dimensions tery) | 100 g (0.22 lbs) 150 mm x 30 mm x 50 mm (5.88 in x 1.25 in x 2 in) | 150 g (0.33 lbs) 165 mm x 32 mm x 50 mm (6.5 in x 1.25 in. x 2 in.) |
| Power | ife (Alkaline) | 1 AA Alkaline | 9 V Alkaline |
| # | umination Light | 10 hours minimum @ 23 °C (73 °F) High Brightness LED | 10 hours minimum @ 23 °C (73 °F) |
| ē. — Ŭ | Iold (7 seconds) | • | High Brightness LED • |
| | dit Display | _ | • |
| Temperat | ture Display | 4 digits, 0.2 °C resolution (0.5 °F) | 4 digits, 0.1 °C resolution (0.2 °F) |
| Max. Tem | np. Displayed | - | · |
| Timer | | - | Integrated countdown timer, adjustable from 10 seconds to 7 hours, 59 minutes |
| Environm | nental | IP54 sealing (hand-washable, non-submersible) | IP54 sealing (hand-washable, non-submersible) |
| Calibratio | on Certificate | - | Calibration accuracy with NIST and DKD traceability |
| Standard | s | Conforms to EN 61326-1 Electromagnetic Emissions and Susceptibility, EN 61010-1 General Safety | Conforms to EN 61326-1 Electromagnetic Emissions and Susceptibility, EN 61010-1 General Safety |
| Certificat | ions | CE NSF | CE NSF |
| Warranty | | 2 year* limited | 2 year* limited |
| - | Accessories | Battery, User's Guide | Battery, Carrying Pouch, User's Manual, Quick Start Guide |
| Options A | Accessories | _ | Replacement Probe |
| -1011011011 | | | noplacement 1 tono |

*US only. Warranty duration may vary.